

Coaxial PCB Connector 82_MFBX-S50-0-6/111_N

Description

Straight PCB jack

Interface Standards
HUBER+SUHNER MFBX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Board mounting type	surface mount
Weight	0.00319 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	PA (Polyamide)	
Insulator	LCP (Liquid crystal polymer)	

Related Documents

Outline drawing	DOU-00245741
Catalogue drawing	DCA-00275283
Mounting hole	DCA-00226318

Ordering Information

Tape and Reel package	82_MFBX-S50-0-6/111_NM
Single package	82_MFBX-S50-0-6/111_NE
Tape and Reel package	82_MFBX-S50-0-6/111_NM-2

Remarks

PCB connector with stand-offs