

Coaxial Cable Connector 16_SMA-50-2-100/199_N

Description

Right angle cable plug

Interface standards

SUHNER-SMA-26.5GHz



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	26.5 GHz

Mechanical Data

Centre contact	plugged
Outer contact	soldered
Weight	0.0056 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	PFA / PTFE	
Coupling nut	Stainless Steel	Passivated (Plating)

Related Documents

Outline drawing	DOU-00072798
Catalogue drawing	DCA-00006235
Assembly instruction	DOC-0000229425

Ordering Information

Bulk 100 pcs package	16_SMA-50-2-100/199_NH
----------------------	------------------------

Additional Information

Suitable cables	EZ_86_TP_M17, SUCOFORM_86, MULTIFLEX_86
-----------------	---