

ATGBICS QSFP-100G-LR4L Cisco Compatible Transceiver QSFP28 100GBase-LR4L (1270/1290/1310/1330nm, SMF, 2km, LC, DOM)

Brand : ATGBICS

Product code: QSFP-100G-LR4L-C



Product name : QSFP-100G-LR4L Cisco Compatible Transceiver QSFP28 100GBase-LR4L (1270/1290/1310/1330nm, SMF, 2km, LC, DOM)


QSFP-100G-LR4L Cisco Compatible Transceiver QSFP28 100GBase-LR4L (1270/1290/1310/1330nm, SMF, 2km, LC, DOM)

ATGBICS QSFP-100G-LR4L Cisco Compatible Transceiver QSFP28 100GBase-LR4L (1270/1290/1310/1330nm, SMF, 2km, LC, DOM):

ATGBICS QSFP-100G-LR4L Cisco Compatible Transceiver QSFP28 100GBase-LR4L aggregates 4 x duplex CWDM Lite, supporting a distance of up to 2km through four independent optical communication lanes. over single-mode fibre (SMF) using wavelengths of 1270/ 1290/ 1310/ 1330nm via an LC connector. Digital optical monitoring (DOM) support is also present enabling real-time monitoring of the parameters of the fibre optic transceiver. Our product meets the specification of QSFP-100G-LR4L and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards.



Performance		Power	
SFP transceiver type *	Fiber optic	Input voltage	3.3 V
Maximum data transfer rate *	100000 Mbit/s	Maximum voltage	3.5 V
Interface type *	QSFP28	Power consumption (typical)	4 W
Single-mode fiber (SMF) supported	✓	Operational conditions	
Multi-mode fiber (MMF) supported	✗	Maximum operating temperature	70 °C
Fiber optic connector	LC	Operating temperature (T-T)	0 - 70 °C
SFP transceiver standard	LR4	Storage temperature (T-T)	-40 - 85 °C
Maximum transfer distance	2000 m	Operating relative humidity (H-H)	0 - 95%
Wavelength	1310 nm	Storage relative humidity (H-H)	0 - 95%
Ethernet LAN	✓	Weight & dimensions	
Ethernet interface type	100 Gigabit Ethernet	Width	13.5 mm
Digital Diagnostics Monitoring (DDM)	✓	Depth	72.4 mm
Features		Height	18.4 mm
Product colour	Silver	Weight	42 g
Housing material	Metal	Packaging data	
Plug and Play	✓	Number of products included	1 pc(s)
Hot-Plug support	✓	Package type	Box
Hot-swap	✓	Technical details	
Easy to install	✓	Sustainability compliance	✓
Country of origin	United Kingdom	Sustainability certificates	RoHS
Brand compatibility	Cisco	Doesn't contain	Lead
Certification	CE, FCC, RoHS		



5056468717085

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.