



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

TE Part #5747089-2
09 RCPT ACT PIN/MS MED STD

TE Part #2170704-2
CAGE ASSY, QSFP28 1X1, SPRING, HS

TE Part #2292069-1
RCPT ASSEMBLY SMT RA 74 POSN MBC

TE Part #2305018-2
USB TYPE C, REC IPX8 ON BOARD DUAL SMT






TE Part #2828384-1

CONN KIT,VITA66.4-DERIV,PLUG,
DUAL-CAVITY



TE Part #316308-000

55A1121-28-0/9-9



TE Part #9-192046-6

LA5(.006) BAND

TE Part #2828455-3

Key Clockable,64 POSN,Custom
Multigig 90

TE Part #2333569-1

TXRX MICROCLIP

TE Part #2371601-1

Dust Cover, HD VITA 66.4 Derivative
Conn

Documents

Product Drawings

Guide Pin Clockable Keyed

English