

Coaxial Cable Connector 21_N-50-10-1/133_U

Description

Straight cable jack

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Centre contact	plugged
Outer contact	crimped
Weight	0.0381 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Brass	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00007459
Catalogue drawing	DOU-00007461
Assembly instruction	DOC-0000343754

Ordering Information

Bulk 50 pcs package	21_N-50-10-1/133_UF
---------------------	---------------------

Additional Information

Suitable cables	S_10162_B-11, S_10172_B-11
-----------------	----------------------------