

Coaxial PCB Connector
82_SMB-S50-0-30/111_N

Description

Straight PCB jack

Interface Standards
IEC 60169-10_MIL-STD-348A/311_CECC 22130



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 4 GHz

Mechanical Data

Board mounting type surface mount
Weight 0.0005 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00449981
Mounting hole DOU-00012611

Ordering Information

Bulk 100 pcs package 82_SMB-S50-0-30/111_NH