

Between Series Adaptor 31_N-716-50-4/133_W

Description

PIM Adaptor jack/jack
N jack (female) / 7/16 jack (female)

Interface standards
Series N - IEC 61169-16_MIL-STD-348A/304_CECC 22210
Series 7/16 - IEC 61169-4_CECC 22190_DIN 47223_VG 95250



Benefits

Low passive intermodulation (PIM) adaptor

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	7.5 GHz
PIM, 3rd order intermodulation distortion (IMD) max.	Static -155 dBc at 2x 43 dBm / 20 W carrier

Mechanical Data

Number of matings	500
Weight	0.0861 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Interface - 7/16 jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00287192
-----------------	--------------

Ordering Information

Single package	31_N-716-50-4/133_WE
----------------	----------------------

Remarks

PIM typ. -160 dBc at 2 x 20 W / 43 dBm