

Coaxial Panel Connector 23_4310-50-0-5/003_-

Description

Straight panel receptacle jack, flange mount

Interface standards
IEC 61169-54



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	12 GHz

Mechanical Data

Number of matings	100
Weight	0.0394 kg

Environmental Data

Operating temperature	-55 °C to 90 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Silver Plating
Outer contact	Bronze	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00263954
Catalogue drawing	DCA-00264946

Ordering Information

Single package	23_4310-50-0-5/003_-E
Tray package	23_4310-50-0-5/003_-Y