

Coaxial Cable Connector 21_SHV-50-4-1/133_N

Description

Straight cable jack

Interface standards

IEC 60498_MIL-STD-348A/314



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	0.3 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0183 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00068587
Catalogue drawing	DOU-00007988
Assembly instruction	DOC-0000832384

Ordering Information

Single package	21_SHV-50-4-1/133_NE
----------------	----------------------

Additional Information

Suitable cables	RG_59_B/U, GX_04273
-----------------	---------------------

Remarks

High voltage connector Working voltage (at sea level) 3.5 kV rms, 50Hz (depending on cable)