

## Coaxial Cable Connector

11\_716-50-7-3/003\_-

### Description

Straight cable plug

Interface standards

IEC 61169-4\_CECC 22190\_DIN 47223\_VG 95250



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	7.5 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.1021 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

### Related Documents

Catalogue drawing	DOU-00007671
Assembly instruction	DOC-0000179879

### Ordering Information

Single package	11_716-50-7-3/003_-E
----------------	----------------------

### Additional Information

Suitable cables	RG_213_/U, GX_07272, G_07262
-----------------	------------------------------