

Coaxial Cable Connector 16_BNC-75-2-3/133_N

Description

Right angle cable plug

Interface standards

Interface compatible with IEC 61169-8



Technical Data

Electrical Data

Impedance	75 Ω
Interface frequency max.	1 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0164 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00071611
Catalogue drawing	DOU-00006046
Assembly instruction	DOC-0000179255

Ordering Information

Single package	16_BNC-75-2-3/133_NE
----------------	----------------------

Additional Information

Suitable cables	RG_179_B/U, RG_187_A/U
-----------------	------------------------