

Coaxial Cable Connector 21_N-50-3-8/133_N

Description

Straight cable jack

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0343 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00006330
Catalogue drawing	DCA-00066586
Assembly instruction	DOC-0000179851

Ordering Information

Bulk 100 pcs package	21_N-50-3-8/133_NH
Single package	21_N-50-3-8/133_NE

Additional Information

Suitable cables	RG_223_/U, ENVIROFLEX_142, RG_142_B/U, RADOX_RF_142
-----------------	---