

Coaxial Cable Connector 16_SMA-50-4-55/199_N

Description

Right angle cable plug

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	plugged
Outer contact	crimped
Weight	0.0093 kg

Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Other body part	Stainless Steel	
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Stainless Steel	
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) / SUCOPRO Plating

Related Documents

Outline drawing	DOU-00007764
Assembly instruction	DOC-0000201296

Ordering Information

Single package	16_SMA-50-4-55/199_NE
----------------	-----------------------

Additional Information

Suitable cables	S_04212_B
-----------------	-----------