

Coaxial Panel Connector 22_SMB-50-0-2/133_N

Description

Straight bulkhead receptacle jack

Interface standards

IEC 60169-10_MIL-STD-348A/311_CECC 22130

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

Mechanical Data

Number of matings	500
Weight	0.0013 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00010650
Catalogue drawing	DCA-00010652
Mounting hole	DOU-00008855

Ordering Information

Bulk 100 pcs package	22_SMB-50-0-2/133_NH
Single package	22_SMB-50-0-2/133_NE