




Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #5499923-3
A/L UNIV HDR 16P VERT LG LAT



TE Part #3-641215-4
04P MTA100 HDR ASSY FL/ST 30AU



TE Part #440055-2
2.0MM,HDR,2POS,R/A




TE Part #350211-1
04P CMNL HDR ASSY PC



TE Part #826926-2
AMPMODU II PIN HEADER




TE Part #0004-058-100L
CONT PIN



TE Part #2008563-1
Connector,1 Pos SMT Poke-In



TE Part #826936-6
6P AMPMODU II STIFT LEI



TE Part #2-2176331-9
CRGP 2512 2K2 1%

Documents

Product Drawings

.058 DIA PIN REC .010TPBECU

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_60983-4_Z.3d_igs.zip

English

Customer View Model

ENG_CVM_60983-4_Z.3d_stp.zip

English

Customer View Model

ENG_CVM_60983-4_Z.2d_dxf.zip

English

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_60983-4_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_60983-4_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_60983-4_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English