

Coaxial Cable Connector 11_716-50-10-3/003_-

Description

Straight cable plug

Interface standards

IEC 61169-4_CECC 22190_DIN 47223_VG 95250



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	7.5 GHz

Mechanical Data

Centre contact	plugged
Outer contact	crimped
Weight	0.1004 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Silver Plating
Outer contact	Brass	Silver Plating
Body	Brass	Silver Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00007919
Catalogue drawing	DOU-00007921
Assembly instruction	DOC-0000183159

Ordering Information

Bulk 10 pcs package	11_716-50-10-3/003_-Z
---------------------	-----------------------

Additional Information

Suitable cables	S_10172_B-11, S_10162_B-11
-----------------	----------------------------