

Coaxial Cable Connector

11_SMA-50-0-150/033_-

Description

Straight cable plug

Interface standards

IEC 60169-15 / Connector for use with SPJ/CPJ Assembly

Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	6 GHz		
Frequency range	DC to 1 GHz	1.7 to 2.7 GHz	3.8 to 6 GHz
Return loss	36 dB	33 dB	26 dB

Mechanical Data

Centre contact	plugged
Outer contact	clamped
Weight	0.0094 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00323218
Assembly instruction	DOC-0000766838

Ordering Information

Single package	11_SMA-50-0-150/033_-E
----------------	------------------------

Additional Information

Suitable cables	SUCOFORM_122_LA_CU_CMP, SUCOFORM_141_LA_CU_CMP, SUCOFORM_141_CU_CMP, SUCOFORM_222_LA_CU_CMP, SPJ/CPJ assemblies
-----------------	---

Remarks

Only in combination with SPJ/PCC assemblies Not valid for direct connection with the SUCOFORM_xxx(_LA)_CU_CMP cables