



Connectors > Connector Accessories > Connector Seals & Cavity Plugs > DEUTSCH Sealing Plugs



Connector Seal & Plug Type: **Keying Plug**
Primary Product Material: **PBT**
Primary Product Color: **Red**
Resistance to Hydrocarbons: **Good**
Operating Temperature (Max): **125 °C [257 °F]**

[All DEUTSCH Sealing Plugs \(10\)](#)

Features

Product Type Features

Connector Seal & Plug Type	Keying Plug
----------------------------	-------------

Body Features

Primary Product Material	PBT
Primary Product Color	Red

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box
------------------	-----

Other

--	--



Resistance to Hydrocarbons	Good
Contains Lubricant	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-H3930-CH8172
DEUTSCH HD30 Housings



TE Part # CAT-H396-CH8172
DEUTSCH HDP20 Housings



TE Part # CAT-D485-CH8172
DEUTSCH DTM Housings



TE Part # CAT-D781-CH8172
DEUTSCH DRB Housings




TE Part # CAT-D799-CH8172
DEUTSCH DRC Housings



TE Part # CAT-ST858-CH8172
DEUTSCH Strike Housings



TE Part # DTM04-12PA-EE04
REC, 12P, BLK, N, HIGH TEMP, A



TE Part # DTM04-08PC
REC, 8P, GRN, N, C



TE Part # DTMH06-4SA
PLG, 4P, BLK, N, HI TEMP, A



TE Part # DRC26-24SB
PLG, 24P, BLK, N, B



TE Part # DRC26-50S09
PLG, 50P, BLK, N, 09




TE Part # DRC26-60S01
PLG, 60P, BLK, N, 01



TE Part # DTM04-3P-R011
REC, 3P, BLK, 90DEG, PANEL



TE Part # DTMH06-2SD
PLG, 2P, BLK, N, HI TEMP, D



TE Part # DRCP28-86SA
PLG, 86P, BLK, 12/20, A



TE Part # DRC26-50S06
PLG, 50P, BLK, N, 06




TE Part # DRC26-60S04
PLG, 60P, BLK, N, 04



TE Part # DRCP24-86PA
REC, 86P, BLK, 12/20, A



TE Part # DRCP26-126SA
PLG, 126P, BLK, 12/20, A



TE Part # DRCP28-86SB
PLG, 86P, BLK, 12/20, B

Also in the Series | **DEUTSCH HD**



Automotive Connector Caps & Covers
(37)



Automotive Housings(742)



Connector Backshells(29)




Connector Seals & Cavity Plugs(10)



Insertion & Extraction Tools(11)



Other Automotive Connector Accessories(11)



PCB Headers & Receptacles(1)

Also in the Series | **DEUTSCH HD30**



Automotive Connector Caps & Covers (19)



Automotive Housings(359)



Connector Backshells(2)



Connector Seals & Cavity Plugs(11)



Insertion & Extraction Tools(10)



Other Automotive Connector Accessories(6)

Customers Also Bought



TE Part #0413-003-1605
SEALING PLUG, SIZE 16, BLU




TE Part #HD34-18-20PN-059
REC,20P,AL,N,CBLCLMP BT,DRAIN,16 /20,P,MC



TE Part #DTP13-4P
HDR, 4P, BLK, RA, SN/NI/CU




TE Part #SRK02-MDA-32A-001
REC, 32P, BLK, E, FLANGE, A



TE Part #1587722-1
CABLE SEAL RETAINER, SIZE A, HVA280-3PM



TE Part #2103306-1
INNER HOUSING, PLUG, HVA280-3PXM, XE



TE Part #1-1534095-1
MQS COVER 2X10P



TE Part #1-1437713-2
106100=GROMMET RED



Documents

Product Drawings
SEALING PLUG, SIZE 20, KEYING, RED
English

CAD Files
3D PDF
3D
Customer View Model
[ENG_CVM_CVM_0413-216-2005_A.2d_dxf.zip](#)
English
Customer View Model
[ENG_CVM_CVM_0413-216-2005_A.3d_igs.zip](#)
English
Customer View Model
[ENG_CVM_CVM_0413-216-2005_A.3d_stp.zip](#)
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
CONNECTOR SELECTOR
English

Product Specifications
Application Specification
English
Application Specification
English
Application Specification
English

Instruction Sheets
Instruction Sheet (U.S.)
English