

Within Series Adaptor 34_TNC-50-0-4/133_N

Description

Bulkhead adaptor jack/jack
TNC-precision jack (female) / TNC-precision jack (female)

For Test & Measurement applications
Precision adaptor

Interface standard
Series TNC-precision - IEC 60169-17_MIL-STD-348A/406_CECC 22200



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz
VSWR	DC - 8 GHz ≤ 1.07 + 0.01 f (GHz)

Mechanical Data

Number of matings	500
Weight	0.0191 kg

Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - TNC-precision jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	

Interface - TNC-precision jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00013576
Mounting hole	DOU-00008751

Ordering Information

Single package	34_TNC-50-0-4/133_NE
----------------	----------------------