

Within Series Adaptor 32_MMBX-50-0-8/111_N

Description

Adaptor plug/plug
MMBX plug (male) / MMBX plug (male)

Slide - snap interface

Interface standard
Series MMBX - SUHNER-MMBX



Technical Data

Electrical Data

Impedance	50 Ω			
Interface frequency max.	12.4 GHz			
Frequency range	DC to 2.5 GHz	2.5 to 6 GHz	6 to 12.4 GHz	
Return loss	≥ 26 dB	≥ 21 dB	≥ 12 dB	

Mechanical Data

Number of matings	100
Weight	0.0003 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - MMBX plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPRO Plating
Body	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE	

Interface - MMBX plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPRO Plating
Body	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00013834
-----------------	--------------

Ordering Information

Single package	32_MMBX-50-0-8/111_NE
----------------	-----------------------