

Coaxial Cable Connector 11_N-50-4-9/133_N

Description

Straight cable plug

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	11 GHz		
Frequency range	DC to 2 GHz	2 to 4 GHz	4 to 6 GHz
Return loss	26 dB	20 dB	19.1 dB

Mechanical Data

Centre contact	plugged
Outer contact	crimped
Weight	0.0254 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00006572
Assembly instruction	DOC-0000180145

Ordering Information

Single package	11_N-50-4-9/133_NE
----------------	--------------------

Additional Information

Suitable cables	SX_04172_B-60, SPUMA_240, LMR-240
-----------------	-----------------------------------