

SENCITY® Omni-M dual-band WiFi Stick Antenna

1355.17.0003

Description

Omni-directional dual-band WiFi stick antenna for application with WiFi standards

IEEE 802.11 a/p/h/b/g/y/n/ac.

Working in the frequency bands 2.3 - 2.5 GHz and 4.8 to 6 GHz.

Gain 6 dBi, vertical polarized antenna.

Ingress protection IP 67 (IEC 60529).

For outdoor and indoor applications

*** Wall- or pole mount with L-bracket ***



Product Configuration

Technical Data

Electrical Data

	Band 1	Band 2	Band 3
Frequency (MHz)	2300 - 2500	4800 - 5150	5150 - 6000
VSWR	1.5	1.7	1.7
Impedance (Ohm)	50	50	50
Gain (dBi)	6	5	6
3dB beamwidth (h) (°)	360	360	360
3dB beamwidth (v) (°)	20	12	12
Composite power max (W)	30	30	30
Ambient temperature (°C)	25	25	25

Ports

	Port 1
Connector	N, jack (female)
Polarization	vertical
DC grounded	No

Connections

	Band 2	Band 3	Band 4
Port 1	X	X	X

General Data

Mechanical Data

Dimensions (mm)	240 x 25 (Height x Diameter)
Weight (kg)	0.3

INCLUDED MOUNTING MATERIAL: Bracket 9091.99.0173 and 2 metal-bands for mast-diameter 25mm - 101mm, all piece parts made of stainless steel

Environmental Data

Environmental conditions	indoor/outdoor
Operation temperature (°C)	-40 to 85
Storage temperature (°C)	-55 to 85
Transport temperature (°C)	-40 to 85
IP rating	IP67
Flammability rating	UL 94-HB
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant
Lead-free soldered	yes
WEEE 2012/19/EU	special marking needed

SENCITY® Omni-M dual-band WiFi Stick Antenna 1355.17.0003

REACH 1907/2006/EC

compliant

LOW TEMPERATURE: IEC 60068-2-1 72h -55°C

HIGH TEMPERATURE: IEC 60068-2-2 72h +85°C

HUMIDITY: ETSI EN300-2-4 T4, 1E 144h 95%

SALT SPRAY: EN 60068-2-11 / GB-T 10125 96h

MECHANICAL SHOCK: IEC 60721-3-4, 4M5

VIBRATION: IEC 60721-3-4 30 min/axis random 4M5

Material Data

Radome colour

RAL 9003 (signal white)

Radome material

Glass Fibre

Related Products

9091.99.0173 L - bracket for omni stick antennas

Related Documents

Mounting instruction

DOC-0000296554

Painting instruction

DOC-0000256180

Security instruction

DOC-0000278984

Outline drawing

DOU-00298652

3D-model

DOC-0000715586