

Within Series Adaptor 31_QLA-01-0-1/112_N

Description

Adaptor jack/jack
QLA-01 jack (female) / QLA-01 jack (female)

Interface standard
Series QLA-01 - NIM-CAMAC-Standard CD/N549



Technical Data

Electrical Data

Impedance other Ω
Interface frequency max. 1.4 GHz

Mechanical Data

Number of matings 10000
Weight 0.0042 kg

Environmental Data

Operating temperature -55 °C to 150 °C
2011/65/EU (RoHS - including compliant
2015/863 and 2017/2102)

Material Data

Interface - QLA-01 jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Bronze	Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	

Interface - QLA-01 jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Bronze	Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing DCA-00013895

Ordering Information

Single package 31_QLA-01-0-1/112_NE