

Coaxial Cable Connector 24_N-50-3-11/133_N

Description

Straight bulkhead cable feed through

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz
Frequency range	DC to 2 GHz
Return loss	29 dB

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0375 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00008899
Catalogue drawing	DCA-00008901
Assembly instruction	DOC-0000179851

Ordering Information

Single package	24_N-50-3-11/133_NE
----------------	---------------------

Additional Information

Suitable cables	RG_58_C/U, G_03232, GX_03272-04
-----------------	---------------------------------