

Within Series Adaptor 32_MBX-50-0-1/133_N

Description

Adaptor plug/plug
MBX plug (male) / MBX plug (male)

Slide - snap interface

Interface standard
Series MBX - HUBER+SUHNER MBX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Number of matings 100
Weight 0.000455 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Interface - MBX plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPLATE (R) Plating
Insulator	PFA / PTFE / LCP	

Interface - MBX plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPLATE (R) Plating
Insulator	PFA / PTFE / LCP	

Related Documents

Outline drawing DPA-00038720

Ordering Information

Bulk 100 pcs package 32_MBX-50-0-1/133_NH
Single package 32_MBX-50-0-1/133_NE

Remarks

Because of the Sucoplate plated adapter the typical values of the outer contact resistance may slightly differ compared to the Sucopro plated adapters.