

Coaxial Cable Connector 11_SK-50-2-51/119_N

Description

Straight cable plug

Interface standards
MIL-STD-348A/323



Technical Data

Electrical Data

Impedance	50 Ω	
Interface frequency max.	40 GHz	
Frequency range	DC to 24 GHz	24 to 40 GHz
Return loss	25 dB	17 dB

Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0027 kg

Environmental Data

Operating temperature	-55 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PPE (Polyphenylene ether, PPO)	
Coupling nut	Stainless Steel	
Gasket	VMQ (Silicone rubber)	

Related Documents

Catalogue drawing	DOU-00007833
Assembly instruction	DOC-0000183051

Ordering Information

Single package	11_SK-50-2-51/119_NE
----------------	----------------------

Additional Information

Suitable cables	EZ_118_TP
-----------------	-----------