

Low Loss 2-way Wilkinson Splitter 380 MHz - 2700 MHz 5501.17.0027

Wilkinson Splitter

Description

This Wilkinson style Power Divider has been designed for low power applications where output isolation is preferable over lowest possible loss. The wide frequency range of this design allows use with multiband antennas and leaky cable systems.

Lower loss dividers which enhance receive sensitivity and preserve transmitted power are available as reactive splitters.

Supports Tetra, Tetrapol, LMR/P25, LTE, UMTS/WCDMA, TD-SCDMA, AMPS, GSM, PCS, CDMA, WiFi / WLAN 2.4 GHz.



Technical Data

Electrical Data

	Signal Band 1	
Frequency	0.38 - 2.7 GHz	
Return Loss input port	17 dB	
Return Loss output port	17 dB	
Splitter Loss	3 dB	
Insertion Loss	0.8 dB	
Isol. between Output ports	20 dB	
Ampl. tra. betw. outp. ports	0.3 dB	
Max. Composite Power	10 W	
	Input 1	
Connector Type	N	
Connector Gender	jack (female)	
	Output 1	Output 2
Connector Type	N	N
Connector Gender	jack (female)	jack (female)
Char. impedance	50 Ω	

Mechanical Data

Dimensions	19.6 x 87 x 102 mm (Height x Width x Length)
Weight	0.37 kg

Environmental Data

Environmental conditions	indoor
Operation temperature	-30 °C to 60 °C
Storage temperature	-30 °C to 60 °C
Transport temperature	-30 °C to 60 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Related Documents

Outline drawing	DPR-00172188
3D-model (Step)	DOC-0000369307

Low Loss 2-way Wilkinson Splitter 380 MHz - 2700 MHz 5501.17.0027

