

Coaxial Cable Connector 21_N-50-7-32/133_N

Description

Straight cable jack

SUHNER full crimp cable attachment
Ingress protection according to IP67



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	11 GHz		
Frequency range	DC to 2 GHz	2 to 4 GHz	4 to 6 GHz
Return loss	≥ 34.5 dB	≥ 29.2 dB	≥ 24.5 dB

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0315 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	SUCOPRO / Gold Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Crimp ferrule	Copper	

Related Documents

Outline drawing	DOU-00165880
Catalogue drawing	DCA-00245549
Assembly instruction	DOC-0000344575

Ordering Information

Single package	21_N-50-7-32/133_NE
----------------	---------------------

Additional Information

Suitable cables	SPUMA_400, SPUMA_400-FR-01, Spuma_400-RS-FR, LMR-400
Interface standards	IEC 61169-16_MIL-STD-348A/304_CECC 22210