

Coaxial Cable Connector 11_TNC-50-4-61/133_N

Description

Straight cable plug

Interface standards

IEC 60169-17_MIL-STD-348A/313_CECC 22200

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Centre contact	plugged
Outer contact	crimped
Weight	0.017414 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Other body part	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00167330
Assembly instruction	DOC-0000347599

Ordering Information

Bulk 100 pcs package	11_TNC-50-4-61/133_NH
----------------------	-----------------------

Additional Information

Suitable cables	SX_04172_B-60
-----------------	---------------