



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2161640-1
EXTRACTION TOOL, PLUG, SMPM



TE Part # 2332708-1
MODULE 8 POS SMPM SNAP-IN DAUGHTERCARD

Also in the Series | AMP VITA 67



Coax Connectors(6)



PCB RF Modules(10)

Customers Also Bought



TE Part #2007394-5
SFP+assy 2x4 Spring Fingers 4



TE Part #6609073-2
30AYT6C J0=F7475B



TE Part #6368150-3
MJ,TE,8P,CAT5,SHIELDED



TE Part #1-406541-8
MJ,INV,1X1,0PNL G.,100"ST,SN



TE Part #5228979-7
JACK,COML,SERIES BNC,GOLD PL




TE Part #EG41050001
ES-CAP-NO.2-B9-0-35MM



TE Part #1054869-1
2084 0000 02



TE Part #1744439-8
EP2.5 Shrd HDR ASSY 8P VERT, GW



TE Part #2101924-4
8 POS PCB MNT RF MODULE W/ PINS & MARK



TE Part #2321032-1
TERMINATOR, SMPM JACK, 50 OHM VITA 67



Documents

Product Drawings

RF BACKPLANE MODULE 8 POS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2157553-1_A_c-2157553-1-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2157553-1_A_c-2157553-1-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2157553-1_A_c-2157553-1-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Products for Aerospace and Defense

English

Instruction Sheets

Instruction Sheet (U.S.)

English