

# DRBF-2A ✓ ACTIVE

DEUTSCH | DEUTSCH DRB

TE Internal #: DRBF-2A

Other Automotive Connector Accessories, Mounting Frame, PA GF, Black, -55 – 125 °C [-67 – 257 °F], DEUTSCH DRB

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Connector Accessories > Other Automotive Connector Accessories >

DEUTSCH DRB Mounting Accessories



Automotive Connector Accessory Type: **Mounting Frame**

Primary Product Material: **PA GF**

Primary Product Color: **Black**

Number of Positions: **48, 60**

Operating Temperature Range: **-55 – 125 °C [-67 – 257 °F]**

[All DEUTSCH DRB Mounting Accessories \(6\)](#)

## Features

### Product Type Features

Automotive Connector Accessory Type	Mounting Frame
-------------------------------------	----------------

### Configuration Features

Number of Positions	48, 60
---------------------	--------

### Body Features

Primary Product Material	PA GF
--------------------------	-------

Primary Product Color	Black
-----------------------	-------

### Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

### Industry Standards

UL Flammability Rating	Not tested
------------------------	------------

### Packaging Features

Packaging Quantity	1
--------------------	---

Packaging Method	Box
------------------	-----

### Other

Serviceable	Yes
-------------	-----

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


## Compatible Parts



Also in the Series | **DEUTSCH DRB**



Automotive Connector Caps & Covers (2)



Automotive Connector Locks & Position Assurance(20)



Automotive Housings(19)



Insertion & Extraction Tools(1)



Other Automotive Connector Accessories(6)

## Customers Also Bought



TE Part #WB-48SA  
WEDGE LOCK, 48P, PLG, GRY, DRB, A



TE Part #2108612-5  
2.05H SPRING FINGER WITH EMBOSS



TE Part #1744426-3  
Header Housing Assy, EP 2.5 RA, 3 Pos.



TE Part #DRB16-48SAE-L018  
PLG, 48P, BLK, E, CAP, A



TE Part #429596-ZZ  
DUST CAP.HD10.WITH 115mm  
NYLON C



TE Part #1062-16-0144-PS  
SOC, SF, SIZE 16, 14-18, AU/SN, 100  
PC



TE Part #2319021-2  
REC CONN CVR,8POS,AMP MCP 2.8,  
FRB



TE Part #6-1437685-4  
8TK2-48=SNAP TRACK



TE Part #0504-002-4001  
DUST CAP, 40P, REC, BLK, AEC

## Documents



### Product Drawings

[FLANGE, MOUNT, 60/48P, BLK, A](#)

English

---

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_DRBF-2A\\_99.2d\\_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_DRBF-2A\\_99.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_DRBF-2A\\_99.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[CONNECTOR SELECTOR](#)

English

---

### Product Specifications

[Application Specification](#)

English