




All Nylon Gold Plated Receptacle: 2.54 mm, no Mating Alignment (89)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Also in the Series

MTA 100

Insertion & Extraction Tools(2)

PCB Connector Covers(69)

PCB Connector Keying(1)

PCB Headers & Receptacles(440)

Standard Rectangular Connectors(495)

Wire-to-Board Connector Assemblies & Housings(1)

Wire-to-Board Connector Contacts(8)

Customers Also Bought

TE Part #3-641126-8
PCB Header: Polyester, Vertical, Unshrouded, No Mating Alignment

TE Part #3-644563-4
04P MTA100 CONN ASSY F/T 24AWG

TE Part #1-86561-0
FFC,PIN CONTACT,LP,ROUND WIRE,

TE Part #641199-5
05P MTA100 CONN ASSY WHT 15AU

TE Part #2118714-2
STD SHIELD FRAME, CRS-13.66X12.70X2.54MM

TE Part #2118713-2
STD SHIELD COVER, CRS-14.06X13.10X2.00MM

TE Part #2-2176330-5
CRGP 2010 1K0 1%

TE Part #4-2176391-5
RQ 1206 35K7 0.1% 10PPM 5K RL

TE Part #130519
TERM, SOLIS, SPADE, 22-16, M4(8)



Documents

Product Drawings

04P MTA100 CONN ASSY GRN 28AWG

English

CAD Files

Customer View Model

ENG_CVM_CVM_641201-4_K.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_641201-4_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_641201-4_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Agency Approvals

Agency Approval Document

English