

Coaxial Cable Connector 11_SK-50-2-60/199_N

Description

Straight cable plug

Interface standards

MIL-STD-348A/323

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	40 GHz
Frequency range	DC to 40 GHz
Return loss	21 dB

Mechanical Data

Centre contact	plugged
Outer contact	soldered
Weight	0.00543 kg

Environmental Data

Operating temperature	-40 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Other body part	Brass	Gold Plating (without Nickel underplating)
Insulator	PPE (Polyphenylene ether, PPO)	
Coupling nut	Stainless Steel	Passivated (Plating)
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00154837
Catalogue drawing	DCA-00221089
Assembly instruction	DOC-0000331903

Ordering Information

Single package	11_SK-50-2-60/199_NE
----------------	----------------------

Additional Information

Suitable cables	MULTIFLEX_86
-----------------	--------------