

Coaxial Cable Connector 16_MBX-50-2-1/113_N

Description

Right angle cable plug

Interface standards

HUBER+SUHNER MBX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.002888 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze / Brass	SUCOPRO Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00162035
Catalogue drawing	DCA-00161645
Assembly instruction	DOC-0000326568

Ordering Information

Single package	16_MBX-50-2-1/113_NE
----------------	----------------------

Additional Information

Suitable cables	ENVIROFLEX_316_D, K_02252_D, G_02232_D
-----------------	--