

Coaxial Panel Connector 22_QN-50-0-1/133_N

Description

Straight bulkhead receptacle jack

Interface standards

QN QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Number of matings	100
Weight	0.012 kg

Environmental Data

Operating temperature	-40 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00010244
Catalogue drawing	DCA-00010246

Ordering Information

Tray package	22_QN-50-0-1/133_NY
--------------	---------------------