

TS-211-GN12

✓ ACTIVE

KISSLING | KISSLING Series TS

TE Internal #: K1143682

Push Button Switches, Single Pole - Double Throw Configuration (Pole-Throw), Switch, Flush Actuator Profile, Threaded, Illuminated, KISSLING Series TS

[View on TE.com >](#)



Relays, Contactors & Switches > Switches > Push Button Switches > Push Button Switch, Center Thread, 1 Actuator, Flush Profile



Configuration (Pole-Throw): **Single Pole - Double Throw**

Push Button Switch Product Type: **Switch**

Actuator Profile: **Flush**

Bushing Style: **Threaded**

Illuminated: **Yes**

[All Push Button Switch, Center Thread, 1 Actuator, Flush Profile \(44\)](#)

Features

Product Type Features

Switch Connection Type	DIN Connector
Push Button Switch Product Type	Switch
Illuminated	Yes
Actuator Style	Round

Configuration Features

Configuration (Pole-Throw)	Single Pole - Double Throw
Snap Action	Without
Support Bracket	Without
Tactile	No
Operating Function	Momentary

Electrical Characteristics

Push Button Switch Voltage Rating	32 VDC
-----------------------------------	--------

Body Features

Actuator Profile	Flush
Bushing Style	Threaded
Actuator Color	Green



Contact Features

Push Button Switch Contact Current Rating	5 A
Switch Contact Plating Material	Silver Clad Copper

Mechanical Attachment

Push Button Switch Mounting Type	Through Hole
----------------------------------	--------------

Housing Features

Process Sealed	No
----------------	----

Operation/Application

Actuator Total Travel	2.5 mm[.098 in]
-----------------------	-----------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # CAT-AL8-STPBSC
Push Button Switch, Center Thread, 1 Actuator, Flush Profile

Also in the Series | KISSLING Series TS

Push Button Switches(73)

Customers Also Bought

TE Part #2141156-2
SWS,8MM HV,WHT,35 SQMM

TE Part #K1146228
Relay 29-321-12B

TE Part #K1164034
Battery Disconnecter 35-513-160-R-A5

TE Part #1-2141154-2
2POS,8MM HV,REC HSG,90DEG,ASSY, SEALED

TE Part #K1018914
Relay 26-27-08

TE Part #K1018878
Relay 26-58-35

TE Part #K1147050
Relay 28-311-99-900

TE Part #K1060010
Relay 30-313-12-901

TE Part #K1157198-4
Toggle Switch 07-2-2-10 939 CV750



Documents

Product Drawings

Push button switch TS-211-GN12

German

Push button switch TS-211-GN12

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_TS-211-GN12_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_TS-211-GN12_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_TS-211-GN12_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

KISSLING PUSH BUTTON SWITCH Series TS

English