

Coaxial PCB Connector 96_QMA-50-0-1/111_N

Description

Straight PCB jack

Interface Standards
QMA QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Board mounting type	through holes
Weight	0.0013 kg

Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PTFE (Polytetrafluoroethylene)	

Related Documents

Outline drawing	DOU-00017485
Catalogue drawing	DCA-00200187
Mounting hole	DCA-00200198

Ordering Information

Bulk 100 pcs package	96_QMA-50-0-1/111_NH
----------------------	----------------------