

Coaxial Cable Connector 21_716-50-12-62/033_-E

Description

Straight cable jack

Interface standards

IEC 61169-4_CECC 22190_DIN 47223_VG 95250



Technical Data

Electrical Data

Impedance	50 Ω	
Interface frequency max.	7.5 GHz	
Frequency range	DC to 2.7 GHz	2.7 to 3.7 GHz
Return loss	32 dB	30 dB

Mechanical Data

Centre contact	plugged
Outer contact	clamped

Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	NR (Natural Rubber)	

Related Documents

Outline drawing	DOU-00332332
Assembly instruction	DOC-0000799919

Ordering Information

Single package	21_716-50-12-62/033_-E
----------------	------------------------

Additional Information

Remarks

Suitable cable: ANDREW/COMMScope AL4RPV-50 / Assembly instructions: Foam-DOC-0000799919, Plenum-DOC-0000736630 /

Note: Use blade unit 74_Z-0-12-21, 85068959 (colour green)