

## SUMMARY

### # Wires



*Image is for illustrative purpose only*

|                  |                         |
|------------------|-------------------------|
| Series           | 0B                      |
| Termination type | No contacts / Accessory |
| IP rating        | 0                       |
| AWG wire size    | 0.00 - 0.00             |
| Cable Ø          | 3.00 - 3.40 mm          |
| Status           | Active                  |

### Download

[Request a quote](#)

[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

|                   |                         |
|-------------------|-------------------------|
| Shell Style/Model | GMA*: Bend relief Green |
| Keying            | No keying               |
| Housing Material  | Silicone elastomer VMQ  |
| Variant           | V : Green               |
| Weight            | .39 g                   |

### Performance

|               |
|---------------|
| Configuration |
| Insulator     |
| Rated Current |


### Others

|                                          |
|------------------------------------------|
| Temp (min / max): -60°C / +200°C         |
| Temperature range in water steam: +140°C |

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

---

# DRAWINGS



No keying

## Dimensions

|     | A    | L    |
|-----|------|------|
| mm. | 3.0  | 27   |
| in. | 0,12 | 1,06 |

---

# RECOMMENDED BY LEMO

## Tools

*LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.*