

ATGBICS 3FE53441AC Nokia Compatible Transceiver SFP 2.4Gbs/1.2Gbs-B+ (Tx1490nm/RX1310nm, 20km, SMF, Ind Temp)

Brand : ATGBICS

Product code: 3FE53441AC-C

Product name : 3FE53441AC Nokia Compatible Transceiver
SFP 2.4Gbs/1.2Gbs-B+ (Tx1490nm/RX1310nm, 20km, SMF,
Ind Temp)



3FE53441AC Nokia Compatible Transceiver SFP 2.4Gbs/1.2Gbs-B+ (Tx1490nm/RX1310nm, 20km, SMF, Ind Temp)

ATGBICS 3FE53441AC Nokia Compatible Transceiver SFP 2.4Gbs/1.2Gbs-B+ (Tx1490nm/RX1310nm, 20km, SMF, Ind Temp):

ATGBICS 3FE53441AC 2.4/1.2Gbs B+ SFP supports a distance of up to 20km over single mode fibre (SMF) using a wavelength of Tx1590nm/Rx1310nm via an SC connector. This bidirectional unit must be used with another transceiver or network appliance of complementing wavelengths. This product is suitable for rugged environments and can operate at temperatures between -40C to +85C. Digital optical monitoring (DOM) support is also present enabling real-time monitoring of the parameters of the fibre optic transceiver. Our product meets the specification of Nokia3FE53441AC= and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards.



Performance		Features	
SFP transceiver type *	Fiber optic	Brand compatibility	Nokia
Maximum data transfer rate *	24000 Mbit/s	Certification	CE, FCC, RoHS
Interface type *	SFP+	Power	
Single-mode fiber (SMF) supported	✓	Input voltage	3.3 V
Multi-mode fiber (MMF) supported	✗	Maximum voltage	3.5 V
Fiber optic connector	SC	Power consumption (typical)	1 W
SFP transceiver standard	BX	Operational conditions	
Maximum transfer distance	20000 m	Storage temperature (T-T)	-40 - 85 °C
Tx wavelength (max)	1490 nm	Operating relative humidity (H-H)	0 - 95%
Rx wavelength (max)	1310 nm	Storage relative humidity (H-H)	0 - 95%
Ethernet LAN	✓	Weight & dimensions	
Ethernet interface type	25 Gigabit Ethernet	Width	13.4 mm
Digital Diagnostics Monitoring (DDM)	✗	Depth	56.5 mm
Features		Height	8.5 mm
Product colour	Silver	Weight	15 g
Housing material	Metal	Packaging data	
Plug and Play	✓	Number of products included	1 pc(s)
Hot-swap	✓	Package type	Box
Easy to install	✓	Technical details	
Country of origin	United Kingdom	Sustainability compliance	✓
		Sustainability certificates	RoHS
		Doesn't contain	Lead



5056468746412

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 15-SEP-2023. Prints or copies of Information are only valid on the printed Publication date