TRACO POWER

Inductor

TCK-116

Order Code	TCK-116
Inductance	10 µH ±20% (at 100 kHz / 250 mV)
Impedance (DCR)	200 mΩ max.
Rated Current	2.3 A max.
Operating Temperature	-40°C to +125°C
RoHS Exemptions	No Exemptions

Impedance Curve



Outline Dimensions



Dimensions [mm]	
A	5.4 max.
B	4.7 ±0.3
C	2.2 max.
D	2.0 ±0.3
E	1.0 ±0.3
F	2.5
G	3.0
H	7.0

All specifications valid at +25°C, unless otherwise stated.

© Copyright 2022 Traco Electronic AG Specifications can be changed without notice.