

ATGBICS CFP2-100G-LR4-OTU4 Cisco Compatible Transceiver CFP2 Module 100GBase-LR4 and OUT4 (1310nm, SMF, 10km, LC, DOM)

Brand : ATGBICS

Product code: CFP2-100G-LR4-OTU4-C

Product name : CFP2-100G-LR4-OTU4 Cisco Compatible Transceiver CFP2 Module 100GBase-LR4 and OUT4 (1310nm, SMF, 10km, LC, DOM)



CFP2-100G-LR4-OTU4 Cisco Compatible Transceiver CFP2 Module 100GBase-LR4 and OUT4 (1310nm, SMF, 10km, LC, DOM)

ATGBICS CFP2-100G-LR4-OTU4 Cisco Compatible Transceiver CFP2 Module 100GBase-LR4 and OUT4 (1310nm, SMF, 10km, LC, DOM). SFP transceiver type: Fiber optic, Maximum data transfer rate: 100000 Mbit/s, Interface type: CFP2. Product colour: Silver, Country of origin: United Kingdom, Brand compatibility: Cisco. Number of products included: 1 pc(s), Package type: Box



Performance		Features	
SFP transceiver type *	Fiber optic	Hot-Plug support	✓
Maximum data transfer rate *	100000 Mbit/s	Hot-swap	✓
Interface type *	CFP2	Easy to install	✓
Single-mode fiber (SMF) supported	✓	Country of origin	United Kingdom
Multi-mode fiber (MMF) supported	✗	Brand compatibility	Cisco
Fiber optic connector	LC	Certification	CE, FCC, RoHS
SFP transceiver standard	LR4	Operational conditions	
Maximum transfer distance	10000 m	Maximum operating temperature	70 °C
Wavelength	1310 nm	Operating temperature (T-T)	0 - 70 °C
Ethernet LAN	✓	Storage temperature (T-T)	-40 - 85 °C
Ethernet interface type	100 Gigabit Ethernet	Operating relative humidity (H-H)	5 - 85%
Networking standards	IEEE 802.3ba	Storage relative humidity (H-H)	5 - 85%
Fiber ethernet cabling technology	100GBASE-LR4	Packaging data	
Digital Diagnostics Monitoring (DDM)	✓	Number of products included	1 pc(s)
Features		Package type	Box
Product colour	Silver	Technical details	
Plug and Play	✓	Sustainability compliance	✓
		Sustainability certificates	RoHS
		Doesn't contain	Lead



5056468729200

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 15-SEP-2023. Prints or copies of Information are only valid on the printed Publication date