

Coaxial Cable Connector 16_N-50-3-15/133_N

Description

Right angle cable plug

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0291 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00005856
Catalogue drawing	DOU-00005858
Assembly instruction	DOC-0000179015

Ordering Information

Bulk 100 pcs package	16_N-50-3-15/133_NH
Single package	16_N-50-3-15/133_NE

Additional Information

Suitable cables	EZ_141_TP_M17, SUCOFORM_141_PE, MULTIFLEX_141
-----------------	---