

Coaxial Cable Connector
16_TNC-50-7-10/133_N

Description

Right angle cable plug

Interface standards
IEC 60169-17_MIL-STD-348A/313_CECC 22200



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 11 GHz

Mechanical Data

Centre contact soldered
Outer contact crimped
Weight 0.0364 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing DOU-00063419
Assembly instruction DOC-0000216795

Ordering Information

Additional Information

Suitable cables S_07262_BD