

SUMMARY

Wires

Low voltage 1



Image is for illustrative purpose only

Series	0M
Termination type	Male crimp
IP rating	68 mated (mating interface)
AWG wire size	24.00 - 20.00
Cable Ø	0.00 - 0.00 mm
Status	Active

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model	FG*: Male crimp contact for M series, standard barrel
Keying	No keying
Housing Material	Gold plated [ISO 27874] brass
Weight	.16 g

Performance

Configuration
Insulator
Rated Current


Others

Humidity (max): 21 days at 95%
Gunfire vibration: 25 Hz - 2000 Hz, 3 axis (Apache helicopter)
Vibration-Sine: 30 g, 3 axes, 12 hr [10 Hz - 2000 Hz]
Vibration-Random: 37.8 g rms - 3 axes, 4 hr amb [50 Hz - 2000 Hz]
Shock Resistance: 300 g [3 ms]

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Lighting strike EIA 364-75: 10K amps - 6 times
Thermal shock: 5 cycles: -65° C to +150° C
EMI Shielding EIA 364-66A: >= 80 dB (1 GHz), >=70 dB (3 GHz), >= 58 dB (6 GHz), >= 40 dB (10 GHz)

DRAWINGS



No keying

Dimensions

	A	C
mm.	0.9	1.1
in.	0,04	0,04

RECOMMENDED BY LEMO

Tools

Crimp Tool: [DPC.91.701.V](#)

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.