

Coaxial PCB Connector 82_MMCX-50-0-8/111_O

Description

Straight PCB jack

Interface Standards
SUHNER-MMCX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Board mounting type	surface mount
Weight	0.0003 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00012947
Catalogue drawing	DCA-00012949
Mounting hole	DCA-00085694

Ordering Information

Tape and Reel package	82_MMCX-50-0-8/111_OM
Single package	82_MMCX-50-0-8/111_OE

Remarks

PCB connector without stand-offs