

Coaxial PCB Connector 85_SMB-Z50-0-19/111_N

Description

Right angle PCB jack

Interface Standards

IEC 60169-10_MIL-STD-348A/311_CECC 22130

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

Mechanical Data

Board mounting type	through holes
Weight	0.0021 kg

Environmental Data

Operating temperature	-40 °C to 100 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Zinc Alloy	SUCOPRO Plating
Body	Zinc Alloy	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00013184
Catalogue drawing	DCA-00013186

Ordering Information

Bulk 100 pcs package	85_SMB-Z50-0-19/111_NH
Single package	85_SMB-Z50-0-19/111_NE

Remarks

PCB connector with stand-offs