

Coaxial Cable Connector 16_QMA-50-4-2/133_N

Description

Right angle cable plug

Interface standards
QMA QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω			
Interface frequency max.	18 GHz			
Frequency range	DC to 2 GHz	2 to 4 GHz		4 to 6 GHz
Return loss	28.5 dB	23.8 dB		23 dB

Mechanical Data

Centre contact	plugged
Outer contact	crimped
Weight	0.0097 kg

Environmental Data

Operating temperature	-40 °C to 80 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00007040
Assembly instruction	DOC-0000197004

Ordering Information

Bulk 100 pcs package	16_QMA-50-4-2/133_NH
Single package	16_QMA-50-4-2/133_NE

Additional Information

Suitable cables	S_04272_B, S_04262_D, SPUMA_240, RFC 12464 , LMR-240
-----------------	--