

2339107-1

✓ ACTIVE


Sliver for SFF-TA-1002

TE Internal #: 2339107-1

Sliver Pigtail Cable Assembly, 124 Position, 30 AWG / 33 AWG,  
 Sliver Plug, High Speed, 0 Power Positions, 124 Signal Positions, UL  
 94V-2

[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > Internal I/O Cable Assemblies



Cable Assembly Type: **Sliver Pigtail**

Connector Type (End A): **Sliver Plug**

Cable Assembly Category: **High Speed**

Number of Positions: **124**

Number of Power Positions: **0**

## Features

### Product Type Features

Cable Assembly Type	Sliver Pigtail
Connector Type (End A)	Sliver Plug
Cable Assembly Category	High Speed

### Configuration Features

Number of Positions	124
Number of Power Positions	0
Number of Signal Positions	124

### Body Features

Cable Flammability Rating	UL 94V-2
---------------------------	----------

### Dimensions

Wire Size	30 AWG, 33 AWG
-----------	----------------

### Operation/Application

Halogen Free	No
--------------	----

## Product Compliance


For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability


### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Also in the Series | Sliver for SFF-TA-1002



## Customers Also Bought



## Documents

### Product Drawings

#### 124PIN SLIVER PLUG KIT.

English

---

### CAD Files

#### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2339107-1\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2339107-1\\_A.3d\\_jgs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2339107-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[Sliver Internal Cabled Interconnect Solutions Brochure \(Chinese\)](#)

---

### Product Specifications

#### Product Specification

English

#### Product Specification

English