

R-8204  ACTIVE

TE Internal #: R-8204

TE Internal Description: RTD,STRR,P100,385,.5%,.030T,H

[View on TE.com >](#)

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

		
TE Part # R-1630 RTD,SM,SR,C10,427,.5%,.05T	TE Part # R-8203 RTD,STRR,C10,427,.5%,.030T,H	TE Part # R-2428 RTD,SM,SR,P100,385,.5%,.06T

Customers Also Bought



TE Part #66602-8
Pin and Socket Contacts, Type III, LP




TE Part #207019-1
METRIMATE PLUG,36 POS




TE Part #284512-4
4 POS TERMI-BLOK HDR 900 POLAR




TE Part #1SNA114836R0000
BAMH



TE Part #1SNA233061R2100
RC610 101->200 VERTICAL



TE Part #1SNA115417R0500
MB6/8.L6



TE Part #1SNA118499R2300
FEM6D



TE Part #R-8203
RTD,STRR,C10,427,.5%,.030T,H

Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_R-8204_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_R-8204_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_R-8204_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[TESS-ANDO-408-000052](#)

English